

LINEA SAFETY

594DUAP100S70-M12X25

EAN 4031582412116



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Linea safety
Type	Automatic locking system
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	120 kg
Load capacity Static	240 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	129 mm
Overall width	83 mm
Overall weight	0.74 kg

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	100 mm
Tread width	20 mm
Hardness of tread (A)	92 Shore A

HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Precision ball bearing
Offset	32 mm
Swivel radius	90 mm
Swivel interference	180 mm
Dome diameter	52 mm
Thread diameter	0 mm

FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem diameter	12 mm
Stem length	25 mm

