

# LEVINA LIGHT

5220PJP100P50

EAN 4031582492750



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	Levina light
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	82 kg
Load capacity Static	164 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	150 mm
Overall weight	0.556 kg

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	100 mm
Tread width	32 mm
Hardness of tread (A)	87 Shore A

## HOUSING

Material fork	Polyamide
Fork shape	Straight
Swivel bearing	Stem, swiveling
Offset	36 mm
Swivel radius	86 mm
Swivel interference	172 mm

## FITTING

Fitting type	Rectangular plate
Plate length	77 mm
Plate width	67 mm
Plate hole length (Minimum)	56 mm
Plate hole length (Maximum)	61.5 mm
Plate hole width (Minimum)	46.5 mm
Plate hole width (Maximum)	51.5 mm
Plate hole diameter	8.5 mm
Bolt hole diameter	11 mm

## FOOT PROTECTION

Suitable wheel diameter	100
-------------------------	-----

# LEVINA LIGHT

5220PJP100P50

EAN 4031582492750



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

