

# KAPPA LOAD

9658FCP160P63

EAN 4031582451924



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement Noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                              |
|-----------------------------|------------------------------|
| Product Name                | Kappa load                   |
| Type                        | Fixed castor                 |
| Standard                    | EN12533 - Heavy Duty Castors |
| Load capacity at 4 km/h     | 900 kg                       |
| Load capacity at 6 km/h     | 750 kg                       |
| Electric Conductive         | No                           |
| Stainless                   | No                           |
| Load capacity Static        | 1800 kg                      |
| Temperature range (Minimum) | -20 °C                       |
| Temperature range (Maximum) | 60 °C                        |
| Overall Height              | 205 mm                       |
| Overall weight              | 3.69 kg                      |

## HOUSING

|                    |                    |
|--------------------|--------------------|
| Housing Material   | Iron forged, heavy |
| Fork shape         | Broad, reinforced  |
| Lubrication nipple | 1                  |

## WHEEL

|                    |                                |
|--------------------|--------------------------------|
| Body material      | Cast iron                      |
| Tread Material Mix | Ultratech Polyurethane, casted |
| Bearing            | Precision ball bearing         |
| Axle               | Screwed with nut               |
| Threadguards       | With threadguard               |
| Diameter           | 160 mm                         |
| Tread width        | 50 mm                          |

## FITTING

|                             |                          |
|-----------------------------|--------------------------|
| Fitting type                | Medium rectangular plate |
| Plate length                | 135 mm                   |
| Plate width                 | 110 mm                   |
| Plate hole length (Maximum) | 105 mm                   |
| Plate hole width (Minimum)  | 75 mm                    |
| Plate hole width (Maximum)  | 80 mm                    |
| Plate hole diameter         | 11 mm                    |

# KAPPA LOAD

9658FCP160P63

EAN 4031582451924



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

