

# KAPPA LOAD

9658MOP300P64

EAN 4031582478860



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Kappa load
Type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	5291.09 lb
Load capacity at 3.7 mph	3968.32 lb
Load capacity Static	10582.18 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall height	13.98 in
Overall weight	34.7 lb

## WHEEL

Body material	Polyamide, super heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	11.81 in
Tread width	3.15 in
Hardness of tread (D)	75 Shore D

## HOUSING

Material	Cast iron, or iron forged, heavy
Fork shape	Broad, reinforced
	✓

## FITTING

Fitting type	Rectangular plate
Plate length	6.89 in
Plate width	5.51 in
Plate hole length (Maximum)	5.51 in
Plate hole width (Maximum)	4.13 in
Plate hole diameter	0.59 in

# KAPPA LOAD

9658MOP300P64

EAN 4031582478860



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

