

LEVINA LIGHT

5225PJP075L51-10 RAL 9011

EAN 4031582482478



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Levina light
Type	Swivel caster with wheel brake
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	165.35 lb
Electric conductive	no
Stainless	no
Load capacity Static	330.69 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	4.06 in
Overall weight	0.39 lb

HOUSING

Housing Material	Polyamide
Fork shape	Straight
Swivel bearing	Stem, swiveling
Housing Color	Graphite black (RAL9011)
Offset	1.06 in
Swivel radius	2.87 in
Swivel interference	5.75 in

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	2.95 in
Tread width	0.98 in
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	0.39 in

LEVINA LIGHT

5225PJP075L51-10 RAL 9011

EAN 4031582482478



BETTER MOBILITY. BETTER LIFE.

Product Drawings

