

AGILA

2477PJO100R47-21,5-24

EAN 4031582326406
Order number 00029023



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Agila |
| Type | Swivel castor with total lock |
| Standard | EN12530 - Devices Castors |
| Load capacity at 1.8 mph | 176.37 lb |
| Load capacity Static | 352.74 lb |
| Temperature range (Minimum) | 14 °F |
| Temperature range (Maximum) | 104 °F |
| Overall height | 5.43 in |
| Overall weight | 1.82 lb |

WHEEL

| | |
|-----------------------|----------------------|
| Body material | Polypropylene |
| Tread material | Thermoplastic rubber |
| Bearing | Plain bearing |
| Threadguards | Without threadguard |
| Diameter | 3.94 in |
| Tread width | 1.26 in |
| Hardness of tread (A) | 87 Shore A |

HOUSING

| | |
|---------------------|---------------------|
| Material | Steel sheet, medium |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Offset | 1.71 in |
| Swivel radius | 5.16 in |
| Swivel interference | 10.31 in |

FITTING

| | |
|----------------------------|--|
| Fitting type | Synthetic expander, square |
| Expander fitting (Minimum) | 0.85 in |
| Expander fitting (Maximum) | 0.94 in |
| Hint | Please indicate required tube innerdiameter when ordering. |

AGILA

2477PJO100R47-21,5-24

EAN 4031582326406
Order number 00029023



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

