

OMIKRON TWIN

9958FTP300P68

EAN 4031582317008
Order number 00801650



BETTER MOBILITY. BETTER LIFE.

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------------------|
| Product name | Omikron twin |
| Housing type | Fixed castor |
| Standard | similar EN12532 - Transport Equipment |
| Load capacity at 2.5 mph | 13227.72 lb |
| Load capacity at 3.7 mph | 8818.48 lb |
| Load capacity Static | 19841.58 lb |
| Temperature range (Minimum) | 14 °F |
| Temperature range (Maximum) | 140 °F |
| Overall height | 16.34 in |
| Overall width | 10.71 in |
| Overall weight | 110.57 lb |

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Casting |
| Tread material | Polyurethane, casted |
| Bearing | Precision ball bearing |
| Axle | Screwed with nut |
| Tread color | Honey yellow (RAL1005) |
| Threadguards | With threadguard |
| Diameter | 11.81 in |
| Tread width | 3.15 in |
| Body width | 3.15 in |
| Hardness of tread (A) | 92 Shore A |
| Hardness of tread (D) | 42 Shore D |

HOUSING

| | |
|---------------|----------------------------------|
| Material | Cast iron, or iron forged, heavy |
| Fork shape | Twin wheel housing |
| Color | Transparent coating |
| Dome diameter | 9.25 in |

FITTING

| | |
|-----------------------------|-------------------|
| Fitting type | Rectangular plate |
| Plate length | 10.63 in |
| Plate width | 9.84 in |
| Plate hole length (Maximum) | 8.27 in |
| Plate hole width (Maximum) | 9.06 in |
| Plate hole diameter | 0.67 in |

OMIKRON TWIN

9958FTP300P68

EAN 4031582317008
Order number 00801650



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

