

STYLEA

5920UOI065L51-11 DOM23x43,6 ALU

EAN 4031582335897



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-------------|
| Roll Performance | ● ● ● ● ○ ○ |
| Movement noise | ● ● ● ● ○ ○ |
| Attrition | ● ● ● ● ● ● |
| Corrosion resistance | ● ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-----------------------------|
| Product name | Stylea |
| Type | Swivel caster |
| Standard | EN12528 - Furniture Castors |
| Load capacity at 1.8 mph | 110.23 lb |
| Electric conductive | no |
| Stainless | no |
| Load capacity Static | 220.46 lb |
| Temperature range (Minimum) | 14 °F |
| Temperature range (Maximum) | 104 °F |
| Overall height | 3.6 in |
| Overall width | 1.81 in |

HOUSING

| | |
|---------------------|--------------------|
| Housing Material | Polyamide |
| Fork shape | Twin wheel housing |
| Swivel bearing | Stem, swiveling |
| Swivel radius | 2.09 in |
| Swivel interference | 4.17 in |
| Dome diameter | 0.91 in |

WHEEL

| | |
|----------------|--------------------------------|
| Body material | Polyamide |
| Tread material | Identical with wheel body |
| Bearing | Plain bearing with spacer tube |
| Axle | Riveted |
| Threadguards | Without threadguard |
| Diameter | 2.56 in |
| Tread width | 0.28 in |

FITTING

| | |
|--------------------|----------------------------|
| Fitting type | Blind hole for B10 fitting |
| Bolt hole diameter | 0.43 in |

STYLEA

5920UOI065L51-11 DOM23x43,6 ALU

EAN 4031582335897



BETTER MOBILITY. BETTER LIFE.

Product Drawings

