

# AGILA TWIN

2977PIP075P30-10

EAN 4031582362329



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Agila twin                    |
| Housing type                | Swivel castor with total lock |
| Standard                    | EN12530 - Devices Castors     |
| Load capacity at 1.8 mph    | 176.37 lb                     |
| Load capacity Static        | 352.74 lb                     |
| Temperature range (Minimum) | -4 °F                         |
| Temperature range (Maximum) | 140 °F                        |
| Overall height              | 3.9 in                        |
| Overall weight              | 1.44 lb                       |

## WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Polypropylene             |
| Tread material        | Solid rubber, non-marking |
| Bearing               | Precision ball bearing    |
| Threadguards          | With threadguard          |
| Diameter              | 2.95 in                   |
| Tread width           | 0.98 in                   |
| Hardness of tread (A) | 75 Shore A                |

## HOUSING

|                     |                     |
|---------------------|---------------------|
| Material            | Steel sheet, medium |
| Fork shape          | Twin wheel housing  |
| Swivel bearing      | Two ball races      |
| Offset              | 1.24 in             |
| Swivel radius       | 3.9 in              |
| Swivel interference | 7.8 in              |

## FITTING

|                    |           |
|--------------------|-----------|
| Fitting type       | Bolt hole |
| Bolt hole diameter | 0.39 in   |

# AGILA TWIN

2977PIP075P30-10

EAN 4031582362329



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

