

# ANIKA

5920UAI065L51-10 DOM18

EAN 4031582433395



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	Anika
Housing type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	50 kg
Load capacity Static	100 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	67 mm
Overall width	39.5 mm
Overall weight	0.075 kg

## WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	65 mm
Tread width	11 mm
Hardness of tread (A)	92 Shore A

## HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Swivel radius	55.5 mm
Swivel interference	111 mm
Dome diameter	18 mm

## FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	10 mm



PRODUCT INFORMATION

# ANIKA

5920UAI065L51-10 DOM18

EAN 4031582433395



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---

