

# DELTA TWIN

9948UOR160P63

EAN 4031582366983  
Order number 00837891



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Delta twin
Housing type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	750 kg
Load capacity at 6 km/h	600 kg
Load capacity Static	1500 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	210 mm
Overall weight	3.066 kg

## WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Roller bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	160 mm
Tread width	40 mm
Hardness of tread (A)	92 Shore A

## HOUSING

Material fork	Iron forged, heavy
Fork shape	Twin wheel housing

## FITTING

Fitting type	Rectangular plate
Plate length	137 mm
Plate width	137 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	11 mm

# DELTA TWIN

9948UOR160P63

EAN 4031582366983  
Order number 00837891



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

