

AGILA TWIN

2977POO75P30-10,3

EAN 4031582428247



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.39 in

CORE ATTRIBUTES

Product name	Agila twin
Housing type	Swivel castor with total lock
Load capacity at 1.8 mph	220.46 lb
Load capacity Static	440.92 lb
Overall height	3.9 in

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	2.95 in
Tread width	0.98 in

HOUSING

Material	Steel sheet, medium
Fork shape	Twin wheel housing
Swivel bearing	Two ball races
Offset	1.22 in
Swivel interference	7.8 in

AGILA TWIN

2977POO75P30-10,3

EAN 4031582428247



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

