

# INTEGRAL TWIN

2940UAP150R05-32

EAN 4031582302516



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Integral twin
Type	Swivel castor
Standard	similar EN12531- Hospital Bed Castors
Load capacity at 3 km/h	150 kg
Load capacity at 4 km/h	150 kg
Load capacity Static	300 kg
Temperature range (Minimum)	-30 °C
Temperature range (Maximum)	80 °C
Overall height	175 mm
Overall width	70 mm
Overall weight	1.545 kg
Certification	Tested and monitored by TÜV Süd

## WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	150 mm
Tread width	15 mm
Hardness of tread (D)	42 Shore D

## HOUSING

Material fork	Steel sheet, medium
Fork shape	Twin wheel housing
Swivel bearing	Precision ball bearing
Offset	45 mm
Swivel radius	120 mm
Swivel interference	240 mm

## FITTING

Fitting type	Solid stem, round
Bolt diameter	32 mm
Bolt length	45 mm



German Design Award



Red Dot Design Award

# INTEGRAL TWIN

2940UAP150R05-32


EAN 4031582302516



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---



German  
Design  
Award



Red Dot  
Design  
Award