

# SCOUT

814WUFC200P60 180° SMART

EAN 4031582429947



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Scout
Housing type	Swivel castor with spring loaded directional lock and wheel brake
Load capacity at 3 km/h	150 kg
Load capacity at 4 km/h	150 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall height	242 mm
Overall width	72 mm
Overall weight	3.143 kg

## WHEEL

Body material	Polyamide
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing, stainless
Threadguards	With threadguard
Diameter	200 mm
Tread width	40 mm
Hardness of tread (A)	64 Shore A

## HOUSING

Material fork	Stainless steel, heavy
Fork shape	Angular
Swivel bearing	Precision ball bearing
Offset	50 mm
Swivel radius	162 mm
Swivel interference	324 mm
Stainless	✓

## FITTING

Fitting type	Rectangular plate
Plate length	130 mm
Plate width	74 mm
Plate hole length (Maximum)	110 mm
Plate hole width (Maximum)	50 mm
Plate hole diameter	10.5 mm

# SCOUT

814WUFC200P60 180° SMART

EAN 4031582429947



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

