

# AGILA TWIN

2977POO75P30-10,3

EAN 4031582428247



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.39 in

## CORE ATTRIBUTES

Product name	Agila twin
Type	Swivel castor with total lock
Load capacity at 1.8 mph	220.46 lb
Load capacity Static	440.92 lb
Overall height	3.9 in

## WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	2.95 in
Tread width	0.98 in

## HOUSING

Material	Steel sheet, medium
Fork shape	Twin wheel housing
Swivel bearing	Two ball races
Offset	1.22 in
Swivel interference	7.8 in

# AGILA TWIN

2977POO75P30-10,3

EAN 4031582428247



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

