

# AGILA

2470UOK050P30-11

EAN 4031582301250



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Agila
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	110.23 lb
Load capacity Static	220.46 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall height	2.72 in
Overall weight	0.42 lb

## WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Cone ball bearing
Threadguards	With threadguard
Diameter	1.97 in
Tread width	0.75 in
Hardness of tread (D)	75 Shore D

## HOUSING

Material	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Offset	0.94 in
Swivel radius	1.93 in
Swivel interference	3.86 in

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.43 in
Hint	Castors can be mounted with standard screws of any length.

# AGILA

2470UOK050P30-11

EAN 4031582301250



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

