

KAPPA LOAD

9651FTP250P64 CL97

EAN 4031582314526
Order number 00863174



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Kappa load
Housing type	Swivel castor with directional lock
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	4761.98 lb
Load capacity at 3.7 mph	3968.32 lb
Load capacity Static	7936.63 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall height	12.01 in
Overall width	5.51 in
Overall weight	35 lb

WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	9.84 in
Tread width	3.15 in
Body width	3.15 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

HOUSING

Material	Cast iron, or iron forged, heavy
Fork shape	Broad, reinforced
Swivel bearing	Deep-groove ball thrust roller bearing
Color	Zink-iron (transparent)
Offset	2.56 in
Swivel radius	7.68 in
Swivel interference	15.35 in
Dome diameter	5.51 in

FITTING

Fitting type	Rectangular plate
Plate length	6.89 in
Plate width	5.51 in
Plate hole length (Maximum)	4.13 in
Plate hole width (Maximum)	5.51 in
Plate hole diameter	0.59 in

KAPPA LOAD

9651FTP250P64 CL97

EAN 4031582314526
Order number 00863174



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

