

# COMPACTA

2198PII036P40-42

EAN 4031582332568



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Compacta
Housing type	Fixed castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	30 kg
Load capacity Static	60 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	50 °C
Overall height	48 mm
Overall weight	0.061 kg

## WHEEL

Body material	Polypropylene
Tread material	Solid rubber, non-marking
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	38 mm
Tread width	15 mm
Hardness of tread (A)	75 Shore A

## HOUSING

Material fork	Steel sheet, medium
Fork shape	Angular
Swivel radius	32 mm

## FITTING

Fitting type	Square plate
Plate length	55 mm
Plate width	25 mm
Plate hole length (Maximum)	45 mm
Plate hole width (Maximum)	45 mm
Plate hole diameter	6 mm

# COMPACTA

2198PII036P40-42

EAN 4031582332568



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

