

# ALPHA STAINLESS

8477UFC125P62

EAN 4031582422559



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ●

## CORE ATTRIBUTES

Product name	Alpha stainless
Housing type	Swivel castor with total lock
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	250 kg
Load capacity Static	500 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall height	155 mm
Overall weight	1.219 kg

## WHEEL

Body material	Polyamide
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing, stainless
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	125 mm
Tread width	40 mm
Hardness of tread (A)	64 Shore A

## HOUSING

Material fork	Stainless steel, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Offset	40 mm
Swivel interference	242 mm
Stainless	✓

## FITTING

Fitting type	Rectangular plate
Plate length	105 mm
Plate width	80 mm
Plate hole length (Minimum)	77 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Maximum)	60 mm
Plate hole diameter	9 mm

# ALPHA STAINLESS

8477UFC125P62

EAN 4031582422559



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

3477U00125P62-neu

