

PRODUCT INFORMATION

# DURATECH

MOP 150X80-Ø35 HL90

EAN 4031582320039  
Order number 00830848



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polyamide, super heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	5.91 in
Tread width	3.15 in
Axle hole diameter	1.38 in
Hub length	3.54 in
Body width	3.15 in
Hardness of tread (D)	75 Shore D
Bearing type	6207

## PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Duratech
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	7936.63 lb
Load capacity at 3.7 mph	6613.86 lb
Load capacity Static	13227.72 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall weight	4.46 lb

# DURATECH

MOP 150X80-Ø35 HL90

EAN 4031582320039  
Order number 00830848



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

