

AGILA STAINLESS

7470PJO075P30-11

EAN 4031582350982
Order number 00036677



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	●●●○○
Movement noise	●●●●●
Attrition	●●●○○
Corrosion resistance	●●●●●

CORE ATTRIBUTES

Product name	Agila stainless
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	165.35 lb
Stainless	✓
Load capacity Static	330.69 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	3.94 in
Overall width	1.69 in
Overall weight	0.5 lb

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Wheel color	Silver gray (RAL7001)
Threadguards	Without threadguard
Diameter	2.95 in
Tread width	0.98 in
Body width	0.98 in
Hardness of tread (A)	87 Shore A

HOUSING

Material	Stainless steel, medium
Fork shape	Broad
Swivel bearing	Two ball races
Color	Stainless steel
Offset	0.94 in
Swivel radius	2.42 in
Swivel interference	4.84 in
Dome diameter	1.69 in

FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.43 in
Hint	Castors can be mounted with standard screws of any length.

AGILA STAINLESS

7470PJO075P30-11

EAN 4031582350982
Order number 00036677



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

