

AGILA STAINLESS

7477PJO075P40

EAN 4031582351033
Order number 00036682



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Agila stainless
Housing type	Swivel castor with total lock
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	75 kg
Load capacity Static	150 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	100 mm
Overall width	43 mm
Overall weight	0.323 kg

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Wheel color	Silver grey (RAL7001)
Threadguards	Without threadguard
Diameter	75 mm
Tread width	25 mm
Body width	25 mm
Hardness of tread (A)	87 Shore A

HOUSING

Material fork	Stainless steel, medium
Fork shape	Broad
Swivel bearing	Two ball races
Colour	Stainless steel
Offset	24 mm
Swivel radius	81 mm
Swivel interference	162 mm
Dome diameter	43 mm
Stainless	✓

FITTING

Fitting type	Square plate
Plate length	60 mm
Plate width	60 mm
Plate hole length (Minimum)	38 mm
Plate hole length (Maximum)	48 mm
Plate hole width (Minimum)	38 mm
Plate hole width (Maximum)	48 mm
Plate hole diameter	6.3 mm

AGILA STAINLESS

7477PJO075P40

EAN 4031582351033
Order number 00036682



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

