

# NOVATECH

FTP 150X50-Ø20 HL60

EAN 4031582329452  
Order number 00800993



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Cast iron              |
| Tread material        | Polyurethane, casted   |
| Bearing               | Precision ball bearing |
| Wheel color           | Honey yellow (RAL1005) |
| Threadguards          | With threadguard       |
| Diameter              | 150 mm                 |
| Tread width           | 50 mm                  |
| Axle hole diameter    | 20 mm                  |
| Hub length            | 60 mm                  |
| Body width            | 50 mm                  |
| Hardness of tread (A) | 92 Shore A             |
| Hardness of tread (D) | 42 Shore D             |

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ● ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                              |
|-----------------------------|------------------------------|
| Product name                | Novatech                     |
| Standard                    | EN12533 - Heavy Duty Castors |
| Load capacity at 4 km/h     | 840 kg                       |
| Load capacity at 6 km/h     | 700 kg                       |
| Load capacity Static        | 1400 kg                      |
| Temperature range (Minimum) | -10 °C                       |
| Temperature range (Maximum) | 60 °C                        |
| Overall weight              | 2.446 kg                     |

## TECHNICAL DRAWINGS

