

# AGILA

2470DIK100R07-Ø21,5-24

EAN 4031582328226  
Order number 00064228



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Agila
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	80 kg
Load capacity Static	160 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	135 mm
Overall width	60 mm
Overall weight	0.959 kg

## WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, non-marking
Bearing	Cone ball bearing
Threadguards	With threadguard
Diameter	100 mm
Tread width	32 mm
Hardness of tread (A)	80 Shore A

## HOUSING

Material fork	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Offset	38 mm
Swivel radius	88 mm
Swivel interference	176 mm
Dome diameter	60 mm

## FITTING

Fitting type	Synthetic expander, round
Expander fitting (Minimum)	22 mm
Expander fitting (Maximum)	24 mm
Hint	Please indicate required tube innerdiameter when ordering.

# AGILA

2470DIK100R07-Ø21,5-24

EAN 4031582328226  
Order number 00064228



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

