

LINEA LIGHT

5925PJ1065S70-10x15/10 scan

EAN 4031582420562



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ● ○

CORE ATTRIBUTES

Product Name	Linea light
Type	Swivel castor with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	25 kg
Electric Conductive	No
Stainless	No
Load capacity Static	50 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall Height	68 mm
Overall width	46 mm
Overall weight	0.13 kg

HOUSING

Housing Material	Polyamide
Fork shape	Twin wheel housing
Swivel Bearing	Stem, swiveling
Swivel radius	67 mm
Swivel interference	134 mm
Dome diameter	23 mm
Thread diameter	0 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Threadguards	Without threadguard
Diameter	65 mm
Tread width	13.9 mm
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem diameter	10 mm
Stem length	15 mm



Deutscher
Designer
Club



Interzum
Award



product
design
award

IF Design
Award

LINEA LIGHT

5925PJ1065S70-10x15/10 scan

EAN 4031582420562



BETTER MOBILITY. BETTER LIFE.

Product Drawings

