

AGILA

2478PJP100P50

EAN 4031582030365
Order number 00006536



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ● ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product name | Agila |
| Type | Fixed castor |
| Standard | EN12530 - Devices Castors |
| Load capacity at 1.8 mph | 220.46 lb |
| Load capacity Static | 440.92 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall height | 5.31 in |
| Overall width | 2.36 in |
| Overall weight | 1.17 lb |

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Polypropylene |
| Tread material | Thermoplastic rubber |
| Bearing | Precision ball bearing |
| Wheel color | Silver gray (RAL7001) |
| Threadguards | With threadguard |
| Diameter | 3.94 in |
| Tread width | 1.26 in |
| Body width | 1.26 in |
| Hardness of tread (A) | 87 Shore A |

HOUSING

| | |
|---------------|---------------------|
| Material | Steel sheet, medium |
| Fork shape | Broad |
| Color | Blue passivated |
| Dome diameter | 2.36 in |

FITTING

| | |
|-----------------------------|-------------------|
| Fitting type | Rectangular plate |
| Plate length | 3.03 in |
| Plate width | 2.64 in |
| Plate hole length (Minimum) | 1.83 in |
| Plate hole length (Maximum) | 2.03 in |
| Plate hole width (Minimum) | 2.2 in |
| Plate hole width (Maximum) | 2.42 in |
| Plate hole diameter | 0.33 in |

AGILA

2478PJP100P50

EAN 4031582030365
Order number 00006536



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

