

LUMINA

6A20POI050B10-11x20

EAN 4031582311310



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○ ○
Movement noise	● ● ● ● ○ ○
Attrition	● ● ● ● ○ ○
Corrosion resistance	● ● ● ● ○ ○

CORE ATTRIBUTES

Product name	Lumina
Type	Swivel caster
Electric conductive	no
Stainless	no
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	2.32 in
Overall width	2.17 in
Overall weight	0.28 lb

HOUSING

Housing Material	Zinc-die-casting / Aluminum
Fork shape	Twin wheel housing, closed
Swivel bearing	Stem, swiveling
Swivel radius	2.01 in
Swivel interference	4.02 in

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	1.97 in
Tread width	0.31 in
Hardness of tread (D)	65 Shore D

FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	0.43 in

LUMINA

6A20POI050B10-11x20

EAN 4031582311310

Order number 00073573

Product Drawings



BETTER MOBILITY. BETTER LIFE.

