

AGILA CARE US

2440PJP200R05-28

EAN 4031582393415



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Agila care US
Type	Swivel caster
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	220.46 lb
Electric conductive	no
Stainless	no
Load capacity Static	440.92 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	9.45 in

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Precision ball bearing
Housing Color	Blue passivated
Offset	2.44 in
Swivel radius	6.38 in
Swivel interference	12.76 in

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	7.87 in
Tread width	1.26 in
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Solid stem, round
Bolt diameter	1.1 in
Bolt length	1.77 in

AGILA CARE US

2440PJP200R05-28

EAN 4031582393415



BETTER MOBILITY. BETTER LIFE.

Product Drawings

