

LINEA LIGHT

5920UOH065L51-10

EAN 4031582403978



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-----------------------------|
| Product name | Linea light |
| Housing type | Swivel castor |
| Standard | EN12528 - Furniture Castors |
| Load capacity at 1.8 mph | 110.23 lb |
| Load capacity Static | 220.46 lb |
| Temperature range (Minimum) | 14 °F |
| Temperature range (Maximum) | 104 °F |
| Overall height | 2.68 in |
| Overall width | 1.81 in |
| Overall weight | 0.2 lb |

WHEEL

| | |
|----------------|---------------------------|
| Body material | Polyamide |
| Tread material | Identical with wheel body |
| Bearing | Plain bearing |
| Threadguards | With threadguard |
| Diameter | 2.56 in |
| Tread width | 0.55 in |

HOUSING

| | |
|---------------------|--------------------|
| Material | Polyamide |
| Fork shape | Twin wheel housing |
| Swivel bearing | Stem, swiveling |
| Swivel radius | 2.2 in |
| Swivel interference | 4.41 in |
| Dome diameter | 0.91 in |

FITTING

| | |
|--------------------|----------------------------|
| Fitting type | Blind hole for B10 fitting |
| Bolt hole diameter | 0.39 in |



LINEA LIGHT


5920UOH065L51-10

EAN 4031582403978



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS



Deutscher
Designer
Club



Interzum
Award



IF
Design
Award