

LUMINA

AA23PJI050L51-10 9011/9011/7042

EAN 4031582413045



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------------------|
| Product name | Lumina |
| Type | Swivel castor with intermittend brake |
| Standard | EN12529 - Swivel Chairs Castors |
| Load capacity at 3 km/h | 40 kg |
| Load capacity Static | 80 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall height | 54 mm |
| Overall width | 55 mm |
| Overall weight | 0.07 kg |

WHEEL

| | |
|-----------------------|--------------------------------|
| Body material | Polypropylene |
| Tread material | Thermoplastic rubber |
| Bearing | Plain bearing with spacer tube |
| Axle | Riveted |
| Tread color | Traffic grey A (RAL7042) |
| Wheel color | Graphite black (RAL9011) |
| Threadguards | Without threadguard |
| Diameter | 50 mm |
| Tread width | 8 mm |
| Axle hole diameter | 0 mm |
| Hub length | 0 mm |
| Body width | 8 mm |
| Hardness of tread (A) | 87 Shore A |

HOUSING

| | |
|---------------------|----------------------------|
| Material fork | Polypropylene |
| Fork shape | Twin wheel housing, closed |
| Swivel bearing | Stem, swiveling |
| Colour | Graphite black (RAL9011) |
| Offset | 20 mm |
| Swivel radius | 52 mm |
| Swivel interference | 104 mm |
| Dome diameter | 0 mm |

FITTING

| | |
|--------------------|--------------------|
| Fitting type | Blind hole for B10 |
| Bolt hole diameter | 10 mm |

PRODUCT INFORMATION

LUMINA

AA23PJI050L51-10 9011/9011/7042

EAN 4031582413045



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

