

INTEGRAL TWIN

2944UAP150R26-28S45 D 9002 4XM8

EAN 4031582302561
Order number 990033077



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ● |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---|
| Product name | Integral twin |
| Type | Swivel castor with central, total or directional lock |
| Standard | EN12531 - Hospital Bed Castors |
| Load capacity at 1.8 mph | 330.69 lb |
| Load capacity at 2.5 mph | 330.69 lb |
| Load capacity Static | 992.08 lb |
| Temperature range (Minimum) | -13 °F |
| Temperature range (Maximum) | 176 °F |
| Overall height | 6.89 in |
| Overall width | 2.95 in |
| Overall weight | 3.13 lb |
| Certification | Tested and monitored by TÜV Süd |

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Polyamide |
| Tread material | Polyurethane, injected |
| Bearing | Precision ball bearing |
| Wheel color | Gray white (RAL9002) |
| Threadguards | With threadguard |
| Diameter | 5.91 in |
| Tread width | 0.59 in |
| Body width | 0.59 in |
| Hardness of tread (A) | 92 Shore A |
| Hardness of tread (D) | 42 Shore D |

HOUSING

| | |
|---------------------|------------------------|
| Material | Steel sheet, medium |
| Fork shape | Twin wheel housing |
| Swivel bearing | Precision ball bearing |
| Color | Gray white (RAL9002) |
| Offset | 1.77 in |
| Swivel radius | 4.88 in |
| Swivel interference | 9.76 in |
| Dome diameter | 2.76 in |

FITTING

| | |
|------------------------------|-------------------------------------|
| Fitting type | Stem with cam hole for profile bars |
| Bolt diameter | 1.1 in |
| Bolt length | 3.78 in |
| Bolt thread position | 0.75 in |
| Bolt mounting holes quantity | 4 |



German Design Award



Red Dot Design Award

INTEGRAL TWIN


2944UAP150R26-28S45 D 9002 4XM8

EAN 4031582302561
Order number 990033077



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS



German
Design
Award



Red Dot
Design
Award