

INTEGRAL TWIN

2940USX125R05-28

EAN 4031582341379



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Integral twin
Housing type	Swivel castor
Standard	similar EN12531- Hospital Bed Castors
Load capacity at 3 km/h	125 kg
Load capacity at 4 km/h	125 kg
Electric conductive	✓
Load capacity Static	250 kg
Temperature range (Minimum)	-30 °C
Temperature range (Maximum)	80 °C
Overall height	150 mm
Overall width	60 mm
Overall weight	1.24 kg
Certification	Tested and monitored by TÜV Süd



German
Design
Award



Red Dot
Design
Award

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected, electric-conductive
Bearing	Precision ball bearing, sealed
Threadguards	With threadguard
Diameter	125 mm
Tread width	12 mm
Hardness of tread (D)	40 Shore D

HOUSING

Material fork	Steel sheet, medium
Fork shape	Twin wheel housing
Swivel bearing	Precision ball bearing
Offset	37.5 mm
Swivel radius	100 mm
Swivel interference	200 mm

FITTING

Fitting type	Solid stem, round
Bolt diameter	28 mm
Bolt length	45 mm
Hint	Washable beds must be sealed in the fitting area by the hospital bed manufacturer.

ADDITIONAL INFORMATION

Washable according AK-BWA

INTEGRAL TWIN



2940USX125R05-28

EAN 4031582341379



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS



German
Design
Award



Red Dot
Design
Award