

# AGILA

2470UOK050P40

EAN 4031582301267



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll Performance	● ● ● ● ● ○
Movement Noise	● ● ● ● ○ ○
Attrition	● ● ● ● ● ●
Corrosion Resistance	● ● ● ● ○ ○

## CORE ATTRIBUTES

Product Name	Agila
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	50 kg
Electric Conductive	No
Stainless	No
Load capacity Static	100 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall Height	69 mm
Overall weight	0.22 kg

## HOUSING

Housing Material	Steel sheet, medium
Fork shape	Broad
Swivel Bearing	Two ball races
Housing Color	Blue passivated
Offset	24 mm
Swivel radius	49 mm
Swivel interference	98 mm

## WHEEL

Body material	Polyamide
Tread Material Mix	Identical with wheel body
Bearing	Cone ball bearing
Threadguards	With threadguard
Diameter	50 mm
Tread width	19 mm
Hardness of tread (D)	75 Shore D

## FITTING

Fitting type	Square plate
Plate length	60 mm
Plate width	60 mm
Plate hole length (Minimum)	38 mm
Plate hole length (Maximum)	48 mm
Plate hole width (Minimum)	38 mm
Plate hole width (Maximum)	48 mm
Plate hole diameter	6.3 mm

# AGILA

2470UOK050P40

EAN 4031582301267



BETTER MOBILITY. BETTER LIFE.

Product Drawings

