

STYLEA

5925UAP100L51-11 DOM41

EAN 4031582370652



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|--------------------------------|
| Product name | Stylea |
| Type | Swivel castor with wheel brake |
| Standard | EN12528 - Furniture Castors |
| Load capacity at 3 km/h | 100 kg |
| Load capacity Static | 200 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 40 °C |
| Overall height | 101 mm |
| Overall width | 75 mm |

WHEEL

| | |
|----------------|------------------------|
| Body material | Polyamide |
| Tread material | Polyurethane, injected |
| Bearing | Precision ball bearing |
| Axle | Riveted |
| Threadguards | With threadguard |
| Diameter | 100 mm |
| Tread width | 20 mm |

HOUSING

| | |
|---------------------|--------------------|
| Material fork | Polyamide |
| Fork shape | Twin wheel housing |
| Swivel bearing | Stem, swiveling |
| Swivel radius | 112 mm |
| Swivel interference | 224 mm |
| Dome diameter | 41 mm |

FITTING

| | |
|--------------------|--------------------|
| Fitting type | Blind hole for B10 |
| Bolt hole diameter | 11 mm |

PRODUCT INFORMATION

STYLEA

5925UAP100L51-11 DOM41

EAN 4031582370652



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

