

KAPPA LOAD

9652FTP200P64 CL97

EAN 4031582314755



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ● ○

CORE ATTRIBUTES

Product Name	Kappa load
Type	Swivel castor with total lock, head end of castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	1680 kg
Load capacity at 6 km/h	1400 kg
Electric Conductive	No
Stainless	No
Load capacity Static	2800 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall Height	255 mm
Overall width	140 mm
Overall weight	14.05 kg

HOUSING

Housing Material	Iron forged, heavy
Fork shape	Broad, reinforced
Swivel Bearing	Deep-groove ball thrust roller bearing
Housing Color	Zink-iron (transparent)
Offset	65 mm
Swivel radius	185 mm
Swivel interference	370 mm
Lubrication nipple	1

WHEEL

Body material	Cast iron
Tread Material Mix	PUR casted premium
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel Color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	200 mm
Tread width	80 mm
Body width	80 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

FITTING

Fitting type	Large rectangular plate
Plate length	175 mm
Plate width	140 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Maximum)	140 mm
Plate hole diameter	15 mm

KAPPA LOAD

9652FTP200P64 CL97

EAN 4031582314755



BETTER MOBILITY. BETTER LIFE.

Product Drawings

