

AGILA

2478PJP075P60-67X60

EAN 4031582302400
Order number 00004810



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila
Housing type	Fixed castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	75 kg
Load capacity Static	150 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	100 mm
Overall width	43 mm
Overall weight	0.201 kg

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Wheel color	Silver grey (RAL7001)
Threadguards	With threadguard
Diameter	75 mm
Tread width	25 mm
Body width	25 mm
Hardness of tread (A)	87 Shore A

HOUSING

Material fork	Steel sheet, medium
Fork shape	Broad
Colour	Blue passivated
Dome diameter	43 mm

FITTING

Fitting type	Rectangular plate
Plate length	67 mm
Plate width	60 mm
Plate hole length (Minimum)	40 mm
Plate hole length (Maximum)	48 mm
Plate hole width (Minimum)	40 mm
Plate hole width (Maximum)	48 mm
Plate hole diameter	6.3 mm

AGILA

2478PJP075P60-67X60

EAN 4031582302400
Order number 00004810



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

