

AGILA CARE US

2444PJP200R26-28S

EAN 4031582393408



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ● ○

CORE ATTRIBUTES

Product Name	Agila care US
Type	Swivel castor with central, total or directional lock
Standard	similar EN12531- Hospital Bed Castors
Load capacity at 3 km/h	100 kg
Load capacity at 4 km/h	100 kg
Electric Conductive	No
Stainless	No
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	240 mm

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Broad
Swivel Bearing	Precision ball bearing
Housing Color	Blue passivated
Offset	62 mm
Swivel radius	162 mm
Swivel interference	324 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	200 mm
Tread width	32 mm
Hardness of tread (A)	87 Shore A

FITTING

Brake cam	hex cam
Fitting type	Stem with cam hole for profile bars
Bolt diameter	28 mm
Bolt length	96 mm

AGILA CARE US

2444PJP200R26-28S

EAN 4031582393408



BETTER MOBILITY. BETTER LIFE.

Product Drawings

