

# KAPPA

9688FTP150P63 CL67 WH-W60

EAN 4031582316131  
Order number 00802031



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	Kappa
Type	Fixed castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	960 kg
Load capacity at 6 km/h	800 kg
Load capacity Static	1600 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall height	200 mm
Overall width	98 mm
Overall weight	5.26 kg

## WHEEL

Body material	Cast iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	150 mm
Tread width	60 mm
Body width	60 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

## HOUSING

Material fork	Iron forged, heavy
Fork shape	Broad, reinforced
Colour	Blue passivated
Lubrication nipple	✓
Dome diameter	96 mm

## FITTING

Fitting type	Medium rectangular plate
Plate length	135 mm
Plate width	110 mm
Plate hole length (Minimum)	75 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	11 mm

# KAPPA

9688FTP150P63 CL67 WH-W60

EAN 4031582316131  
Order number 00802031



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

