

LUMINA

AA29PJI050L51-10 BRAKE UNDER LOAD

EAN 4031582437522



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Lumina
Housing type	Customized solution
Standard	EN12528 - Furniture Castors
Load capacity Static	176.37 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	2.13 in
Overall width	2.17 in
Overall weight	0.15 lb

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	1.97 in
Tread width	0.39 in
Hardness of tread (A)	87 Shore A

HOUSING

Material	Polypropylene
Fork shape	Twin wheel housing, closed
Swivel bearing	Stem, swiveling
Offset	0.79 in
Swivel radius	2.01 in

FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	0.39 in

PRODUCT INFORMATION

LUMINA

AA29PJI050L51-10 BRAKE UNDER LOAD

EAN 4031582437522



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

