

AGILA

2470YGO100P50

EAN 4031582343380



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-------------|
| Roll Performance | ● ● ● ● ○ ○ |
| Movement Noise | ● ● ● ● ● ○ |
| Attrition | ● ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product Name | Agila |
| Type | Swivel castor |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 80 kg |
| Electric Conductive | Yes |
| Stainless | No |
| Load capacity Static | 160 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall Height | 135 mm |
| Overall width | 60 mm |
| Overall weight | 0.59 kg |

HOUSING

| | |
|---------------------|---------------------|
| Housing Material | Steel sheet, medium |
| Fork shape | Broad |
| Swivel Bearing | Two ball races |
| Housing Color | Blue passivated |
| Offset | 38 mm |
| Swivel radius | 88 mm |
| Swivel interference | 176 mm |
| Dome diameter | 60 mm |

WHEEL

| | |
|-----------------------|---|
| Body material | Polypropylene, electric conductive |
| Tread Material Mix | Thermoplastic rubber, electric-conductive |
| Bearing | Plain bearing |
| Wheel Color | Silver grey (similar RAL7001) |
| Threadguards | Without threadguard |
| Diameter | 100 mm |
| Tread width | 32 mm |
| Body width | 32 mm |
| Hardness of tread (A) | 87 Shore A |

FITTING

| | |
|-----------------------------|-------------------|
| Fitting type | Rectangular plate |
| Plate length | 77 mm |
| Plate width | 67 mm |
| Plate hole length (Minimum) | 46.5 mm |
| Plate hole length (Maximum) | 51.5 mm |
| Plate hole width (Minimum) | 56 mm |
| Plate hole width (Maximum) | 61.5 mm |
| Plate hole diameter | 8.5 mm |

AGILA

2470YGO100P50

EAN 4031582343380

Order number 00036788
Product Drawings



BETTER MOBILITY. BETTER LIFE.

