

# KAPPA

9682TOP150P63 CL67

EAN 4031582316049  
Order number 00803482



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	Kappa
Type	Swivel castor with total lock, head end of castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	2116.44 lb
Load capacity at 3.7 mph	1763.7 lb
Load capacity Static	3527.39 lb
Temperature range (Minimum)	-22 °F
Temperature range (Maximum)	176 °F
Overall height	7.87 in
Overall width	4.57 in
Overall weight	9.2 lb

## WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	5.91 in
Tread width	1.97 in
Body width	1.97 in
Hardness of tread (D)	75 Shore D

## HOUSING

Material	Cast iron, or iron forged, heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races, reinforced or stainless
Color	Blue passivated
Offset	2.28 in
Swivel radius	5.41 in
Swivel interference	10.83 in
	✓
Dome diameter	4.37 in

## FITTING

Fitting type	Rectangular plate
Plate length	5.31 in
Plate width	4.33 in
Plate hole length (Minimum)	2.95 in
Plate hole length (Maximum)	3.15 in
Plate hole width (Minimum)	2.95 in
Plate hole width (Maximum)	4.13 in
Plate hole diameter	0.43 in

# KAPPA

9682TOP150P63 CL67

EAN 4031582316049  
Order number 00803482



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

