

# KAPPA

9681IFP250P63 CL67

EAN 4031582366174  
Order number 00838194



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ● ● |
| Movement noise       | ● ● ● ● ● |
| Attrition            | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ● ● |

## CORE ATTRIBUTES

|                             |                                     |
|-----------------------------|-------------------------------------|
| Product name                | Kappa                               |
| Type                        | Swivel castor with directional lock |
| Standard                    | EN12532 - Transport Equipment       |
| Load capacity at 4 km/h     | 500 kg                              |
| Load capacity at 6 km/h     | 400 kg                              |
| Load capacity Static        | 1000 kg                             |
| Temperature range (Minimum) | -20 °C                              |
| Temperature range (Maximum) | 85 °C                               |
| Overall height              | 305 mm                              |
| Overall width               | 110 mm                              |
| Overall weight              | 5.901 kg                            |

## WHEEL

|                       |                                       |
|-----------------------|---------------------------------------|
| Body material         | Aluminium                             |
| Tread hardness        | soft                                  |
| Tread material        | Elastic tire, non-marking, vulcanized |
| Bearing               | Precision ball bearing                |
| Axle                  | Screwed with nut                      |
| Wheel color           | Grey / non marking                    |
| Threadguards          | Without threadguard                   |
| Diameter              | 250 mm                                |
| Tread width           | 50 mm                                 |
| Body width            | 50 mm                                 |
| Hardness of tread (A) | 68 Shore A                            |

## HOUSING

|                     |   |
|---------------------|---|
| Material fork       | Iron forged, heavy                      |
| Fork shape          | Broad, reinforced                       |
| Swivel bearing      | Two ball races, reinforced or stainless |
| Colour              | Blue passivated                         |
| Offset              | 61 mm                                   |
| Swivel radius       | 187.5 mm                                |
| Swivel interference | 375 mm                                  |
| Lubrication nipple  | ✓                                       |
| Dome diameter       | 111 mm                                  |

## FITTING

|                             |                          |
|-----------------------------|--------------------------|
| Fitting type                | Medium rectangular plate |
| Plate length                | 135 mm                   |
| Plate width                 | 110 mm                   |
| Plate hole length (Minimum) | 75 mm                    |
| Plate hole length (Maximum) | 80 mm                    |
| Plate hole width (Minimum)  | 75 mm                    |
| Plate hole width (Maximum)  | 105 mm                   |
| Plate hole diameter         | 11 mm                    |

# KAPPA

9681IFP250P63 CL67

EAN 4031582366174  
Order number 00838194



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

