

# AGILA

2477UAP150R05-25.4

EAN 4031582403497



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Agila
Housing type	Swivel castor with total lock
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	220.46 lb
Load capacity Static	440.92 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall height	7.4 in
Overall weight	2.94 lb

## WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	5.91 in
Tread width	1.26 in
Hardness of tread (D)	40 Shore D

## HOUSING

Material	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Offset	1.42 in
Swivel radius	5.16 in
Swivel interference	10.31 in

## FITTING

Fitting type	Solid stem, round
Bolt diameter	1 in
Bolt length	1.77 in

# AGILA

2477UAP150R05-25.4

EAN 4031582403497



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

