

OMIKRON TWIN

9950FTP250P68

EAN 4031582316810

Order number 00801114

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Omikron twin
Type	Swivel caster
Standard	similar EN12532 - Transport Equipment
Load capacity at 2.5 mph	11023.1 lb
Load capacity at 3.7 mph	7936.63 lb
Electric conductive	no
Stainless	no
Load capacity Static	16534.65 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall height	14.37 in
Overall width	10.71 in
Overall weight	120.06 lb



BETTER MOBILITY. BETTER LIFE.

HOUSING

Housing Material	Cast iron, or iron forged, heavy
Fork shape	Twin wheel housing
Swivel bearing	Deep-groove ball thrust roller bearing
Housing Color	Transparent coating
Offset	2.76 in
Swivel radius	8.29 in
Swivel interference	16.57 in
Lubrication nipple	1
Dome diameter	9.86 in

WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	9.84 in
Tread width	3.15 in
Body width	3.15 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

FITTING

Fitting type	Rectangular plate
Plate length	10.63 in
Plate width	9.84 in
Plate hole length (Maximum)	8.27 in
Plate hole width (Maximum)	9.06 in
Plate hole diameter	0.67 in

OMIKRON TWIN

9950FTP250P68

EAN 4031582316810

Order number 00801114
Product Drawings



BETTER MOBILITY. BETTER LIFE.

9950...250P68

