

KAPPA LOAD

9658FCP200P63

EAN 4031582451931



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Kappa load
Type	Fixed castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	1400 kg
Load capacity at 6 km/h	1200 kg
Load capacity Static	2800 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	305 mm
Overall weight	4.585 kg

WHEEL

Body material	Cast iron
Tread material	Ultratech Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	200 mm
Tread width	50 mm

HOUSING

Material fork	Iron forged, heavy
Fork shape	Broad, reinforced
Lubrication nipple	✓

FITTING

Fitting type	Medium rectangular plate
Plate length	135 mm
Plate width	110 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	11 mm

KAPPA LOAD

9658FCP200P63

EAN 4031582451931



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

