

# LINEA LIGHT

5925XSO075L51-10 RAL7001

EAN 4031582399127  
Order number 00770565



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ● ● |
| Movement noise       | ● ● ● ● ● |
| Attrition            | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ● ● |

## CORE ATTRIBUTES

|                             |                                |
|-----------------------------|--------------------------------|
| Product name                | Linea light                    |
| Housing type                | Swivel castor with wheel brake |
| Standard                    | EN12528 - Furniture Castors    |
| Load capacity at 1.8 mph    | 198.42 lb                      |
| Electric conductive         | ✓                              |
| Load capacity Static        | 396.83 lb                      |
| Temperature range (Minimum) | -4 °F                          |
| Temperature range (Maximum) | 140 °F                         |
| Overall height              | 2.97 in                        |
| Overall width               | 2.17 in                        |
| Overall weight              | 0.33 lb                        |

## WHEEL

|                       |   |
|-----------------------|---|
| Body material         | Polyamide, electric conductive              |
| Tread material        | Polyurethane, injected, electric-conductive |
| Bearing               | Plain bearing                               |
| Threadguards          | Without threadguard                         |
| Diameter              | 2.95 in                                     |
| Tread width           | 0.59 in                                     |
| Hardness of tread (A) | 92 Shore A                                  |

## HOUSING

|                     |                    |
|---------------------|--------------------|
| Material            | Polyamide          |
| Fork shape          | Twin wheel housing |
| Swivel bearing      | Stem, swiveling    |
| Offset              | 0.91 in            |
| Swivel radius       | 3.19 in            |
| Swivel interference | 6.38 in            |
| Dome diameter       | 1.18 in            |

## FITTING

|                    |                            |
|--------------------|----------------------------|
| Fitting type       | Blind hole for B10 fitting |
| Bolt hole diameter | 0.39 in                    |



Deutscher Designer Club



Interzum Award



IF Design Award

# LINEA LIGHT


5925XSO075L51-10 RAL7001

EAN 4031582399127  
Order number 00770565



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS



Deutscher  
Designer  
Club



Interzum  
Award



IF  
Design  
Award