

LUMINA

AA25PJI050S70-8X15 TFR

EAN 4031582389142



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Lumina
Housing type	Swivel castor with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	40 kg
Load capacity Static	80 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	54 mm
Overall width	55 mm
Overall weight	0.095 kg

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	50 mm
Tread width	10 mm
Hardness of tread (D)	65 Shore D

HOUSING

Material fork	Polypropylene
Fork shape	Twin wheel housing, closed
Swivel bearing	Stem, swiveling
Swivel radius	63 mm
Swivel interference	126 mm
Thread diameter	8 mm

FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem length	15 mm