

LEVINA LIGHT

5225PJP075L51-10 RAL 9011

EAN 4031582482478



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ● ○

CORE ATTRIBUTES

Product Name	Levina light
Type	Swivel castor with wheel brake
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	75 kg
Electric Conductive	No
Stainless	No
Load capacity Static	150 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall Height	103 mm
Overall weight	0.18 kg

HOUSING

Housing Material	Polyamide
Fork shape	Straight
Swivel Bearing	Stem, swiveling
Housing Color	Graphite black (RAL9011)
Offset	27 mm
Swivel radius	73 mm
Swivel interference	146 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	75 mm
Tread width	25 mm
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Blind hole for B10
Bolt hole diameter	10 mm

LEVINA LIGHT

5225PJP075L51-10 RAL 9011

EAN 4031582482478



BETTER MOBILITY. BETTER LIFE.

Product Drawings

