

LINEA LIGHT

5927UAI075P41-42X42 EN12528 RAL7001

EAN 4031582415421



BETTER MOBILITY. BETTER LIFE.




Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Linea light |
| Housing type | Swivel castor with total lock |
| Standard | EN12528 - Furniture Castors |
| Load capacity at 1.8 mph | 132.28 lb |
| Load capacity Static | 264.55 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall height | 3.43 in |
| Overall width | 2.17 in |
| Overall weight | 0.53 lb |

WHEEL

| | |
|----------------|--------------------------------|
| Body material | Polyamide |
| Tread material | Polyurethane, injected |
| Bearing | Plain bearing with spacer tube |
| Threadguards | Without threadguard |
| Diameter | 2.95 in |
| Tread width | 0.59 in |

HOUSING

| | |
|---------------------|--------------------|
| Material | Polyamide |
| Fork shape | Twin wheel housing |
| Swivel bearing | Stem, swiveling |
| Offset | 0.91 in |
| Swivel radius | 3.23 in |
| Swivel interference | 6.46 in |

FITTING

| | |
|-----------------------------|--------------|
| Fitting type | Square plate |
| Plate length | 1.65 in |
| Plate width | 1.65 in |
| Plate hole length (Maximum) | 1.26 in |
| Plate hole width (Maximum) | 1.26 in |
| Plate hole diameter | 0.2 in |



PRODUCT INFORMATION

LINEA LIGHT


5927UAI075P41-42X42 EN12528 RAL7001

EAN 4031582415421



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS



Deutscher
Designer
Club



Interzum
Award



IF
Design
Award