

# AGILA

2470DIK100P30-13 TFR

EAN 4031582394894



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	Agila
Type	Swivel caster
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	176.37 lb
Electric conductive	no
Stainless	no
Load capacity Static	352.74 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	185 °F
Overall height	5.31 in
Overall weight	1.86 lb

## HOUSING

Housing Material	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Housing Color	Blue passivated
Offset	1.5 in
Swivel radius	3.46 in
Swivel interference	6.93 in

## WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, non-marking
Bearing	Cone ball bearing
Threadguards	With threadguard
Diameter	3.94 in
Tread width	1.26 in
Hardness of tread (A)	80 Shore A

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.51 in
Hint	Castors can be mounted with standard screws of any length.

# AGILA

2470DIK100P30-13 TFR

EAN 4031582394894



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

